

LDP1000 SERIES



GAS PURIFIER COMPATIBLE WITH ANY TRACE GAS ANALYSIS SYSTEM

The LDP1000 series is a sub ppb purifier used for generating high purity calibration gas for online analyzers as well as generating high purity carrier gas for gas chromatograph.

Designed with two steps of purification, this purifier design ensures no undesired impurity is released during process.

WHY CHOOSING LDP1000 SERIES ?

- **2 beds of purification**
Allows perfect purification
- **RS-232 port**
Monitor the temperature of the 2 beds of purification
- **LEDs indication**
Self-diagnostic and status of the purifier
- **Cost effective solution for long-term use**
Interchangeable getter
- **Available in different format**
Compact version makes it ideal when space is limited
- **Real end of life monitoring**
Combined with PED technology and MultiDetek series, LDP1000 series gas purity can be monitored in real time to offer real auto diagnostic.



SPECIFICATIONS:

GETTER TYPE	Alloy of Zr/V/Fe 2 beds (350 and 200 Celsius)
GASES PURIFIED	Ar/He/Ne/Xe/Kr - Nitrogen and hydrogen version available
IMPURITIES REMOVED	H ₂ O, O ₂ , CO, CO ₂ , N ₂ , THC, H ₂ , CH ₄ (heated) H ₂ O, O ₂ , CO, CO ₂ , H ₂ (room temperature)
IMPURITY LEVEL	<10 ppb and <1 ppb available
FLOW	Compact & LDP1000 versions flow rate are 0.2LPM nominal to 1LPM maximal Large LDP1000 version flow rate is 2LPM nominal to 10LPM maximal
GAS CONNECTIONS	1/8" - 1/4" compression or VCR®
RECOMMENDED OPERATING PRESSURE	100 PSIG (689 kPAG)
SUPPLY	120 VAC, 50 - 60 Hz or 220 VAC, 50 - 60 Hz
POWER CONSUMPTION	Start-up : maximum 200 Watts (allows quick start-up) Normal operation : maximum 50 Watts (designed for low consumption)
WEIGHT	8 lbs (3.63 kg) Large LDP1000 • 5 lbs (2.26 kg) LDP1000 • 2 lbs (0.90 kg) Compact-LDP1000


CERTIFICATION:

CE In compliance with EMC directive 2004/108/EC, EN 61000-6-2:2005 for immunity & EN 61000-6-4:2007 for emissions.


ORDERING INFORMATION:

LDP1000, LARGE LDP1000, COMPACT LDP1000, GETTER LDP1000 OR MINI LDP1000	-XXX	-X	-X	-X	-X
	Operating Voltage: 120 volts (-120) 220 volts (-220)	Gas type: N: Noble gases N2: Nitrogen version H2: Hydrogen	Connection size: 1/8" 1/4"	Connection Type: Compression (-C) VCR (-V)	Supporting plate: P-1/8C: Stainless steel supporting plate/ 1/8" compression with high purity bypass valve & 2 in/out isolation valves P-1/8V: Stainless steel supporting plate/ 1/8" VCR with high purity bypass valve & 2 in/out isolation valves P-1/4C: Stainless steel supporting plate/ 1/4" compression with high purity bypass valve & 2 in/out isolation valves P-1/4V: Stainless steel supporting plate/ 1/4" VCR with high purity bypass valve & 2 in/out isolation valves None: no plate

DIMENSIONS LDP1000:



DIMENSIONS COMPACT-LDP1000:



990 Monfette Est, Thetford Mines, (Qc), Canada, G6G 7K6
Phone: 418 755-1319 • Fax: 418 755-1329 • info@ldetek.com

www.ldetek.com